




High Security 3 in 1 Locking System

Kenstan locks featuring Mul-T-Lock® core.

To Start:

- The lock is installed by a Professional Locksmith.
- Use the GREEN dotted key.



When you need to CHANGE your lock COMBINATION:


- Open the YELLOW pouch, insert the yellow dotted key and operate the lock. The green key is now disabled.
- Use the YELLOW dotted key.

When you need to CHANGE your lock COMBINATION:

- Open the RED pouch, insert the red dotted key and operate the lock. The yellow key is now disabled.
- Use the RED dotted key.

Two Position Maintained Switch locks

Double pole double throw Toggle Switch rated 10 amp/250VAC, 15 amp/125VAC with screw terminal. This lock is available in Keymatic, Medeco®, Medeco Removable Core, ASSA®, I.C. Core, Disc Tumbler, CyberLock® and Mul-T-Lock® Keyways. Call Kenstan for more information and options.



Through Bolt and Drawer Pull Mount Plate

- Steel plate has tapped holes that will permit lock to be installed with machine screws.
- Drawer pull or knob is through bolted for a secure installation.
- Six additional holes are provided to mount the plate to the drawer face.
- Slot accommodates various size drawer pulls.